	M 320	M 320FB	P 310
GENERAL			
Warm-up time	30 seconds	30 seconds	26 seconds
First copy speed: BW		7.1 seconds	
Continuous output speed		32 ppm	
Memory: standard	256 MB	256 MB	128 MB
Weight	18 kg	18 kg	13 kg
Dimensions: W x D x H	405 x 392 x 407 mm	405 x 392 x 420 mm	370 x 392 x 262 mm
Power source	220 - 240 V, 50 - 60 Hz	220 - 240 V, 50 - 60 Hz	220 - 240 V, 50 - 60 Hz
Laser classification		Class 1 Laser Product (IEC60825 - 1:2014)	
COPIER			
Multiple copying	-	Up to 99 copies	-
Resolution	-	1,200 x 1,200 dpi	-
Zoom	-	From 25% to 400% in 1% steps	-
PRINTER			
Printer language: standard	PCL5e (M	AC), PCL6 (Windows & Linux), PostScript3	(Windows)
Print resolution: maximum	1,200 x 1,200 dpi		
Network interface: standard	C41	nernet 10 base-T/100 base-TX, USB2.0 Type	a B
Network interface: option	• • • • • • • • • • • • • • • • • • • •		
Windows® environments	Windows® 8.1, Windows® 10, Windows® Server 2012, Windows® Server 2012R2, Windows® Server 2016, Windows® Server		
		2019	
Mac OS environments		Macintosh OS X v10.10 or later	
Other supported environments		Linux environment	
SCANNER			
Scanning: B/W	13 ipm	13 ipm	-
Scanning: full colour	4.5 ipm	4.5 ipm	-
Resolution: maximum	600 dpi	600 dpi	-
FAX			
Compatibility	-	ITU-T (CCITT) G3	-
Transmission speed	-	seconds	-
Modem speed: maximum	-	Kbps	-
PAPER HANDLING			
		Other dead managements (a) (AA AE AC DE DO)	
Recommended paper size	Standard paper tray(s) (A4, A5, A6, B5, B6)		
Paper input: standard		300 sheets	
Paper input: maximum		550 sheets	
Paper output: standard	50 sheets	50 sheets	125 sheets
Paper weight		52 - 162 g/m²	
ECOLOGY			
Power consumption: operation	514 W	520 W	512 W
Power consumption: sleep	0.87 W	0.87 W	0.72 W
TEC*	0.423 kWh/week	0.423 kWh/week	0.408 kWh/week
INPUT/OUTPUT TRAYS AND FI	NISHER OPTIONS		
1x 250-sheet paper tray			
Bridge unit			
CONSUMABLES			
Starter toner		1,000 prints	
Toner (regular yield)	3,500 prints		
		•	
Toner (high yield)		prints	
Consumable yield measuring			

Ricoh Nederland B.V.

Hambakenwetering 1 5231 DD 's Hertogenbosch The Netherlands



(0)73 - 645 1333





method ISO/IEC 19752